



# R4-IBT-1400-300-300-400-400-920 Performance Curves



Max Sizeable RPM = 1000 RPM. Curve shown extended beyond this point for reference only.



Notes:

The static pressure of non-woven polyester filters is 2 times the static pressure of standard EZ Klean Filters.

The static pressure of throw-away filters is 1.33 times the static pressure of standard EZ Klean Filters.

The static pressure of throw-away MERV 13 filters is 1.9 times the static pressure of standard EZ Klean Filters.

Throw-away filters are used in v-bank intakes only.

